


M

IRALAN

2.4G IrDA In-ear Controller Non-chamber Diagram



Power parameter meter

LOAD: YJ-(50-70)W×2

OUTPUT: 90V-140VDC 240mA±5%

INPUT: AC180-266V 50/60Hz

Ta: -20...45°C Tc: 65°C

Separate Full Bright Fan (High) Full Bright (Mid Fan) (High)

Intelligent control, Overtemperature protection,

Overvoltage protection, Overcurrent protection

In order to enhance the remote control receiving signal, please expose the infrared probe outside the lamp body.




RoHS



M

IRALAN

2.4G IrDA In-ear Controller Non-chamber Diagram



Power parameter meter

LOAD: YJ-(50-70)W×2

OUTPUT: 90V-140VDC 240mA±5%

INPUT: AC180-266V 50/60Hz

Ta: -20...45°C Tc: 65°C

Separate Full Bright Fan (High) Full Bright (Mid Fan) (High)

Intelligent control, Overtemperature protection,

Overvoltage protection, Overcurrent protection

In order to enhance the remote control receiving signal, please expose the infrared probe outside the lamp body.



RoHS

