


# INSTRUCTION MANUAL



## Chuck DL

<p>1.</p>	<p>2.</p> <p>∅80mm</p>	
<p>3.</p> <p>INPUT: AC220-240V</p>	<p>4.</p> <p>FREE SPACE ≥10CM</p>	<p>5.</p> <p>warning: when replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>6.</p>	<p>Overall Sizes:</p> <p>inner small ring</p> <p>40°</p> <p>Chuck DL Round</p> <p>102mm ∅92mm</p> <p>Chuck DL Square</p> <p>102mm 92mm</p>	