


FOR A GOOD REASON GRUNDIG


- Ⓚ Wrist blood pressure monitor
- Easy to read LCD display
- Ⓚ Blutdruckmessgerät für das Handgelenk
- Leicht ablesbares LCD-Display
- Ⓚ Moniteur de pression sanguine au poignet
- Affichage LCD facile à lire
- Ⓚ Pots-bloeddrukmeter
- Gemakkelijk af te lezen lcd-display
- Ⓚ Tensiometro de muñeca
- Pantalla LCD fácil de leer
- Ⓚ Misuratore di pressione da polso
- Display LCD di facile lettura
- Ⓚ Medidor de tensão arterial para pulso
- Ecrã LCD de fácil leitura
- Ⓚ Ranteesta mittaava verenpainemittari
- Helppolukuinen nestekidenäyttö
- Ⓚ Blodtrykksmåler til håndledd
- Lett å lese LCD-skjerm
- Ⓚ Blodtrycksmätare för handled
- Lättläst LCD-display
- Ⓚ Blodtrykksmåler til håndled
- Lettlæselig LCD-skærm
- Ⓚ Vérnyomásfigyelő csuklóra
- Könnyen olvasható LCD-kijelző
- Ⓚ Апарат за измерване на кръвно налягане за китка
- LCD дисплей с лесно разчитане
- Ⓚ Tensiometru pentru încheietura mâinii
- Afişaj LCD ușor de citit
- Ⓚ Plakoměr na zápěstí
- Dobře čitelný displej LCD
- Ⓚ Plakomer na zápästie
- Dobre čitateľný displej LCD
- Ⓚ Plakomjer za zapešče
- LCD zaslon koji se lako čita
- Ⓚ Ciśnieniomierz nadgarstkowy
- Czytelny wyświetlacz LCD
- Ⓚ Riešo kraujospūdžio ekranas
- Paprasta skaityti LCD ekraną
- Ⓚ Тонометр на запястьє
- с удобным ЖК-дисплеєм
- Ⓚ Randme vererõhuarvamat
- Lihtsasti loetav LCD-ekraan
- Ⓚ Asinsspiediena mēritājs apakšdelmam
- Viegli nolasaāms LCD displejs
- Ⓚ Bilekten tansiyon ölçer
- Okunması kolay LCD ekran
- Ⓚ Πιεσοόμετρο καρπού
- Οθόνη LCD με εύκολη ανάγνωση



iHealthLabs Europe SAS
36 Rue de Ponthieu, 75008, Paris, France



ANDON HEALTH CO., LTD No. 3 Jinping Street,
YaAn Road, Nankai District, Tianjin
300190, China



SPECIFICATION

Measuring method: Oscillometric method, automatic inflation and measurement
Memory volume: 2x60 times with time and date stamp
Battery information: 2xAAA (1.5V) included
Measurement range:
Cuff pressure: 0-300mmHg
Systolic: 60-260mmHg
Diastolic: 40-199mmHg
Pulse rate: 40-180 beats/minute
Pressure: ±3mmHg
Pulse rate: Less than 60: ±3bpm more than 60(incl.) ±5%
Precision of the displayed values: 1mmHg
Environmental temperature for operation: 10°C ~ 40°C(50°F ~ 104°F)
Environmental humidity for operation: <85%RH
Environmental temperature for storage and transport: -20°C ~ 50°C(-4°F ~ 122°F)
Environmental humidity for storage and transport: <85%RH
Environmental pressure: 80kPa-105kPa
Cuff circumference: 14.0-19.5cm

Batch:

ITEM NO. 47437



8 711252 474373 >

2X

AAA/LR03

INCL.

© copyright Edco Deutschland GmbH, Siemensstr.
31 47533 Kleve Deutschland. Made in P.R.C.

© The Grundig trademark is used under license
Edco UK Ltd, 1st Floor Two Chamberlain Square,
B3 3AX, Birmingham, UK

Made in P.R.C. © copyright