


# INSTRUCTION MANUAL



Alloy DL White Adjustable 94870  
 Alloy DL Black Adjustable 104843  
 Alloy DL Black Gold Adjustable 104844



<p>1.</p>	<p>2.</p>	<p>3.</p>
<p>4.</p> <p>INPUT: AC220~240V</p>	<p>5.</p>	<p>6.</p> <p>Warning: When replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>7.</p>	<p>Overall Sizes:</p>	