


Product structure diagram



- ① HD camera
- ② MAC hole
- ③ Treble
- ④ USB 2.0


Installation steps

1. Turn on the Camera Mount and point the camera toward the front of the display.
2. Press down on the Camera Mount and snap the rear end of the screen mount to the back of the screen.
3. Plug the USB data cable into the USB interface of the computer.

Detail parameter

Webcam parameters	
Driving type	Plug and play without driver
Photo format	BMP
Sensor type	CMOS
Scintillation control	50Hz
focusing range	80cm
Support device	Support mainstream computer Windows 2000, XP, XP2, Vista, Win7, Win8, Win10, Mac OS, Linux operating system
USB line length	> 1.40cm
Resolving power	1920x1080
Interface type	USB2.0
Microphone	Built-in microphone
Product size	70x61.7x44mm

Product accessories



Webcam instructions*1

Webcam*1