


LURK®

User Manual

Professionele Video Fotografie**Ring of Light 12" Studio by LURK®**

LU-ROL004

**Specifications:**


Parameters	Model	LU-ROL004
Material		ABS/PC/Metal rod
Power		10W
Charging		USB
LED Light beads		96pcs
Input		DC 5V 2A
Product size		30x200CM

Product accessories:



26cm LED ring light	1pc
170cm Stand	1pc
15.5cm Soft metal tube cellphone holder	1pc
56cm Microphone holder rod+Microphone clip	1pc
Microphone	1pc
Bluetooth remote	1pc
Adapter	1pc
Camera holder	1pc
Instructions	1pc

Related Notes


1. Hand press the switch for 2 seconds to turn on/off.
2. Light mode: Slightly touch the switch to change the light color, followed by white, warm light, cold & warm light.
3. Brightness adjustment: 10 levels brightness, pressing "+" means the light is getting stronger and stronger, pressing "-" is getting weaker and weaker.
4. Memory function: When you switch on the fill light again, it still retains the same light mode as last time.

Installation method:

4. Take ② out of the box, screw the other end into the hole of ①. Flexible metal tube phone holder installing finished. (as shown)




6. To remove the phone holder and then take ② out of the box. Mount ② onto the light as picture. Loosen the side screw of ②, then mount the top of ② to the bottom of camera and twist the part counterclockwise properly. Tighten the side screw. Camera holder installed.

**LURK®**

Gebruikershandleiding NL

Professionele Video Fotografie**Ring Of Light 12" Studio by LURK®**

LU-ROL004

**Specificaties:**


Model	LU-ROL004
Materiaal	ABS/PC/METAAL
Vermogen	10W
Opladen	USB/ADAPTER
LED lampen	120 stuks
Input	DC 5V 2A
Afmetingen	30x200CM

Product Accessoires:



Ring Of Light 12"	1st
Verstelbaar statief (tot 170cm)	1st
Flexibele neck met telefoon houder	1st
Microfoon houder	1st
Microfoon	1st
Bluetooth afstandsbediening	1st
Adapter	1st
(actie)camera houder	1st
Handleiding	1st

Overige opmerkingen:

1. houdt de aan/uit knop voor 2 seconden vast om de lamp aan of uit te zetten.
2. Licht standen: Druk rustig op de aan/uit knop om de kleur van de lamp te verstellen naar wit licht, warm licht en natuurlijk licht.
3. Contrast sterkte: De Ring Of Light heeft 10 standen welke zijn te verstellen met de "+" en de "-".
4. De Ring Of Light onthoudt de instellingen die jij hebt gekozen wanneer je de lamp aanzet.

Installatie voorschriften:

4. Haal de flexibele nek (2) uit de verpakking en draai deze vast in de ringlamp (1). Plaats uw mobiele telefoon in de houder. (zie foto)



6. Om je (actie)camera te gebruiken verwijder je flexibele nek met telefoon houder. Vervolgens pak je de camera houder (6), en draai deze vast op locatie waar de flexibele nek bevestigd was. Nu kan je camera op de draaibare balhoofd bevestigen. (zie foto)

